
### Rittal – The System.

Faster – better – everywhere.





# SV 9683.660 Partial Mounting Panel

State: 2025-10-30 (Source: rittal.com/ca-en)



# SV 9683.660 - Partial Mounting Panel for compartment side panel

With or without cable entry, for direct attachment to compartment side panel.

#### **Features**

Model No.	SV 9683.660
Version	Solid
Product description	For direct attachment to the compartment side panel for internal compartmentalization. Universal internal installation with switchgear and control devices. Creation of additional mounting levels. In combination with compartment dividers and side panels, internal partitioning in accordance with Form 1 to 4 is possible.
Material	Carbon steel, 2 mm
Surface finish	Zinc-plated
Supply includes	Angle brackets and assembly components
For compartment height	1,000 mm
Dimensions	Width: 502 mm Height: 993 mm
Suitable for	Width: = 600 mm
Packaging unit	1 pc(s).
Net weight	11.64
Gross weight	12.12
PCF/VE (cradle-to-gate)	45.9 kg CO2 eq (Cat B)
Information regarding the PCF class	Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared
Customs tariff number	94039910
EAN	4028177935303
ETIM 9	EC000213

© Rittal 2025

#### Features

ECLASS 8.0

27400613

## **Approvals**

Explanations

Declaration of conformity UK

© Rittal 2025

3