Rittal – The System.

Faster – better – everywhere.





CS 9783.550 Outdoor Basic enclosure

State: 2025-11-04 (Source: rittal.com/ca-en)



CS 9783.550 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles







Features

Model No.	CS 9783.550
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated
	UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured
	Basic enclosure with gland plate, three-part
	25 mm system punchings in the roof, base, front and in the enclosure depth
	Front door(s) with door stay, swing lever handle and semi-cylinder lock BJ20027
	Transport plinth with screw-fastened trim panels front and rear
	Rain canopy
Dimensions	Width: 600 mm
	Height: 1,200 mm
	Depth: 400 mm

© Rittal 2025

Features

Dimensions	Overall height: 1,355 mm Rain canopy width: 650 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 512 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height of base/plinth: 100 mm
Type rating according to UL 50E	Type 3R
Protection category IP to IEC 60 529	IP 55
IK code	IK10
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	38.95
Gross weight	41
EAN	4028177569157
ETIM 9	EC000261
ECLASS 8.0	27180101

© Rittal 2025 3