Rittal – The System.

Faster – better – everywhere.





CS 9783.610 **Outdoor Basic enclosure**

State: 2025-10-19 (Source: rittal.com/ca-en)



CS 9783.610 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles







Features

Model No.	CS 9783.610
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated
	UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured
	Basic enclosure with gland plate, three-part
	25 mm system punchings in the roof, base, front and in the enclosure depth
	Front door(s) with door stay, swing lever handle and semi-cylinder lock BJ20027
	Transport plinth with screw-fastened trim panels front and rear
	Rain canopy
Dimensions	Width: 800 mm
	Height: 1,200 mm
	Depth: 500 mm

© Rittal 2025

Features

Dimensions	Overall height: 1,355 mm		
	Rain canopy width: 850 mm		
	Rain canopy height: 55 mm Rain canopy depth: 550 mm Clearance width: 712 mm Clearance height: 1,112 mm Clearance depth: 449 mm		
		Height of base/plinth: 100 mm	
		Number of doors	1
		Type rating according to UL 50E	Type 3R
		Protection category IP to IEC 60 529	IP 55
	IK code	IK10	
Base material	Aluminum		
Packaging unit	1 pc(s).		
Net weight	34		
Gross weight	36.15		
EAN	4028177569171		
ETIM 9	EC000261		
ECLASS 8.0	27180101		

Approvals

onformity

© Rittal 2025