

Rittal – The System.

Faster – better – everywhere.



CS 9784.540

Outdoor Basic enclosure

State: 2026-05-04 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9784.540 - Outdoor Basic enclosure

Single-walled housing systems, one-door and two-door. Ready for use for all applications with passive interior equipment or low power dissipation in outdoor areas. Roof concept with all-round louvred grilles



Features

Model No.	CS 9784.540
Product description	Outdoor housing with 100 mm transport base/plinth and rain canopy projecting on all sides.
Material	Aluminum AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Color	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and semi-cylinder, lock BJ20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy
Dimensions	Width: 1,200 mm Height: 1,200 mm Depth: 500 mm

Features

Dimensions	Overall height: 1,355 mm Rain canopy width: 1,250 mm Rain canopy height: 55 mm Rain canopy depth: 550 mm Clearance width: 1,112 mm Clearance height: 1,112 mm Clearance depth: 449 mm Height of base/plinth: 100 mm
Design Centre bar	With removable centre bar, 2 lockable doors
Number of doors	2
Type rating according to UL 50E	Type 3R
Protection category IP to IEC 60 529	IP 55
IK code	IK10
Note	Enclosure with width 1200 mm has two 600 mm-wide mounting panels
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	66 kg
Gross weight	71 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	Outdoor basic enclosure, WHD: 1,200 x 1,200 x 500 mm, aluminum, with 100 mm transport base/plinth and rain canopy, double doors on front

Approvals

Explanations	Declaration of conformity
--------------	---------------------------