

Rittal – The System.

Faster – better – everywhere.



CS 9791.045

Outdoor Wall-mounted enclosure

State: 2026-03-25 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9791.045 - Outdoor Wall-mounted enclosure

Outdoor housings for wall or pole mounting. Enclosure-within-an-enclosure concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation.



Features

Model No.	CS 9791.045
Product description	Outdoor housings for wall or pole mounting. Housing-within-a-housing concept, outer enclosure with cut-out at the bottom and integrated louvers on the rear and side panels for ventilation
Material	Enclosure and mounting plate: Aluminum AlMg3 Door inner casing: Stainless steel 1.4301 (AISI 304)
Surface finish	Housing: powder-coated, UV-resistant pure polyester
Color	RAL 7035
Supply includes	Double-walled outdoor housing, fully preconfigured Inner enclosure with mounting plate, gland plate and security lock Mounting bracket for enclosure internal thermostat or hygromat Outer housing with designer cover and security lock 3524 E 2 C rails on the rear panel 2 security locks
Dimensions	Width: 630 mm Height: 780 mm Depth: 380 mm

Features

Clearances	Clearance width: 560 mm Clearance height: 560 mm Clearance depth: 308 mm
Dimensions of mounting plate (W x H)	550 mm x 550 mm
Inner housing	Width: 580 mm Height: 580 mm Depth: 333 mm
Lock	Lock version: Cam No. of locks: 2
Protection category IP to IEC 60529	IP 55
Note	Delivery times on request.
Base material	Aluminum
Packaging unit	1 pc(s).
Net weight	22.254 kg
Gross weight	23.425 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101
Product description	CS Wall-mounted enclosure, WHD: 630x780x380 mm, aluminum, with mounting plate, Enclosure-within-an-enclosure concept

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---