

Rittal – The System.

Faster – better – everywhere.



AX 9792.065

Outdoor enclosure

State: 2026-02-14 (Source: rittal.com/ca-en)



AX 9792.065 - Outdoor enclosure for AX wallmount enclosure

Housing for AX compact enclosures for outdoor use, consisting of enclosure shell, rear panel, base and plug-in door. For creating an enclosure-within-an-enclosure concept. Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation.



Features

Model No.	AX 9792.065
Product description	Housing for AX compact enclosures, for use outdoors. For creating an enclosure-within-an-enclosure concept. Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation.
Benefits	Housing for AX compact enclosures, for use outdoors For creating an enclosure-within-an-enclosure concept Cut-out at the bottom and integrated louvres in the side and base for optimum enclosure ventilation
Material	Aluminum AlMg3
Surface finish	Powder-coated
Supply includes	Support rails for wall mounting Brush strip Stepped collar M25 Cam lock with 3 mm double-bit insert Incl. grounding and assembly components

Features

Note	Depending on the application/environment, a carbon steel or stainless steel enclosure may be built into the housing
Dimensions	Width: 621 mm Height: 650 mm Depth: 308 mm
Suitable for	Enclosure type: AX Width: = 500 mm Height: = 500 mm Depth: = 210 mm
Packaging unit	1 pc(s).
Net weight	15.6
Gross weight	16.2
Customs tariff number	94032080
EAN	4028177961784
ETIM 9	EC000261
ECLASS 8.0	27180101