

**Rittal – The System.**

Faster – better – everywhere.



# SZ 9968.112 Enclosure Light

State: 2026-06-22 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 9968.112 - Enclosure Light

Rittal's fluorescent lights are designed for quick and easy installation. The external terminal block means no need to disassemble the light to make electrical connections. Equipped with interference suppression capacitor or a RFI filter, they also come with or without a lamp shade or 115 V U.S. style receptacle.

## Features

Model No.	SZ 9968.112
Benefits	Designed for quick and easy installation External terminal block allows no need to disassemble the light to make electrical connections Available in 15 or 18 watt rating, they can be used with or without the Rittal door switch. Equipped with interference suppression capacitor or a RFI filter, they also come with or without a lamp shade or 115 V U.S. style receptacle.
Material	Lamp holder: polycarbonate Switch: polyester and polycarbonate Terminal block: nylon
Color	RAL 7044
Supply includes	Fasteners
Connection options	L1, N, GND
Light (bulb)	Cool white fluorescent
Switch (type)	On/off rocker switch
Light – installation type	TS vertical profile, direct TS roof frame (horizontal profile), direct
Light – installation type	Screw fastening
Luminous flux	1,170 lm
Dimensions	Width: 620 mm Height: 110 mm Depth: 45 mm

# Features

---

Packaging unit	1 pc(s).
Net weight	5 lb
Gross weight	5.071 lb
Customs tariff number	9403999040

---