

Rittal – The System.

Faster – better – everywhere.



undefined 9980.095

NEMA 3R Vented Outdoor Enclosure

State: 2025-08-17 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



undefined 9980.095 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.



Features

| | |
|---------------------|---|
| Model No. | 9980.095 |
| Product description | The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters. |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010) |
| General color | RAL 9003 |
| Color | White |
| Supply includes | Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 609 mm Height: 869 mm Depth: 304 mm |
| Dimensions of mounting plate (W x H) | 549 mm x 730 mm |
| Lock | Lock version: Cam No. of locks: 2 Lock Insert: Screwdriver |
| Type rating according to UL 50E | UL Type 3R UL Type 1 UL Type 12 |
| Protection category NEMA | NEMA 3R NEMA 1 NEMA 12 |
| Material thickness - door | 2 mm |
| Material thickness - enclosure | 1.5 mm |
| Material thickness – mounting plate | 2.5 mm |
| Rated current | 0.46 A |
| Air throughput (unimpeded air flow) | 150 cfm |
| Fan Size | 4 in |
| Weight/packaging unit | 96 lb. |
| Packaging unit | 1 pc(s). |
| Net weight | 96.109 |
| UPC-Code | 92346 |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|