Rittal - The System.

Faster – better – everywhere.





undefined 9980.095 NEMA 3R Vented Outdoor Enclosure

State: 2025-11-25 (Source: rittal.com/ca-en)



undefined 9980.095 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.







Features

| Model No. | 9980.095 |
|---------------------|--|
| Product description | The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes predrilled mounting holes and integrated cooling with fans and filters. |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010) |
| General color | RAL 9003 |
| Color | White |
| Supply includes | Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits |

© Rittal 2025 2

Features

| Dimensions | Width: 609 mm |
|--------------------------------------|--------------------------|
| | Height: 869 mm |
| | Depth: 304 mm |
| Dimensions of mounting plate (W x H) | 549 mm x 730 mm |
| Lock | Lock version: Cam |
| | No. of locks: 2 |
| | Lock Insert: Screwdriver |
| Type rating according to UL 50E | UL Type 3R |
| | UL Type 1 |
| | UL Type 12 |
| Protection category NEMA | NEMA 3R |
| | NEMA 1 |
| | NEMA 12 |
| Material thickness - door | 2 mm |
| Material thickness - enclosure | 1.5 mm |
| Material thickness – mounting plate | 2.5 mm |
| Rated current | 0.46 A |
| Air throughput (unimpeded air flow) | 150 cfm |
| Fan Size | 4 in |
| Weight/packaging unit | 96 lb. |
| Packaging unit | 1 pc(s). |
| Net weight | 96.109 |
| Customs tariff number | 9403999040 |
| UPC-Code | 92346 |

Approvals

© Rittal 2025 3

Approvals

Approvals

UL + C-UL (listed)

© Rittal 2025 4