

Rittal – The System.

Faster – better – everywhere.



undefined 9980.097

NEMA 3R Vented Outdoor Enclosure

State: 2026-02-06 (Source: rittal.com/ca-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

undefined 9980.097 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.



Features

| | |
|---------------------|---|
| Model No. | 9980.097 |
| Product description | The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters. |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel Mounting plate: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated Seal: Blue, dyed (RAL 5010) |
| General color | RAL 9003 |
| Color | White |
| Supply includes | Housing with vented roof module Door with fitted seal and vented hood Mounting panel Top-mounted 115V fans Thermostat Washable Filter kits |

Features

| | |
|--------------------------------------|--|
| Dimensions | Width: 609 mm Height: 1,184 mm Depth: 354 mm |
| Dimensions of mounting plate (W x H) | 540 mm x 1,020 mm |
| Lock | Lock version: Cam No. of locks: 3 Lock Insert: Screwdriver |
| Type rating according to UL 50E | UL Type 3R UL Type 1 UL Type 12 |
| Protection category NEMA | NEMA 3R NEMA 1 NEMA 12 |
| Material thickness - door | 2 mm |
| Material thickness - enclosure | 2 mm |
| Material thickness – mounting plate | 2.5 mm |
| Rated current | 0.34 A |
| Air throughput (unimpeded air flow) | 250 cfm |
| Fan size | 6 in |
| Packaging unit | 1 pc(s). |
| Net weight | 131.001 |
| Gross weight | 131.001 |
| Customs tariff number | 9403999040 |
| UPC-Code | 92348 |

Approvals

Approvals

Approvals

UL + C-UL (listed)