Rittal – The System.

Faster – better – everywhere.



# undefined 9980.098

# NEMA 3R Vented Outdoor Enclosure

State: 2026-11-02 (Source: www.rittal.com/ca-en)

# undefined 9980.098 - NEMA 3R Vented Outdoor Enclosure

The Wall-Mounted NEMA 3R Vented Outdoor Enclosure is a single door enclosure with roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters.







## Features

| | |
|---|---|
| Model No. | 9980.098 |
| Product description | The NEMA 3R Vented Outdoor Enclosure is a single door enclosure with a roof module and door hood. The configuration includes pre-drilled mounting holes and integrated cooling with fans and filters. |
| Material | Door: Carbon steel, all-round foamed-in PU seal<br>Housing: Carbon steel<br>Mounting plate: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting panel: Zinc-plated<br>Seal: Blue, dyed (RAL 5010) |
| General color | RAL 9003 |
| Color | White |
| Supply includes | Housing with vented roof module<br>Door with fitted seal and vented hood<br>Mounting panel<br>Top-mounted 115V fans<br>Thermostat<br>Washable Filter kits |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 909 mm<br>Height: 1,334 mm<br>Depth: 404 mm |
| Dimensions of mounting plate (W x H) | 840 mm x 1,155 mm |
| Lock | Lock version: Cam<br>No. of locks: 3<br>Lock Insert: Screwdriver |
| Type rating according to UL 50E | UL Type 3R<br>UL Type 1<br>UL Type 12 |
| Protection category NEMA | NEMA 3R<br>NEMA 1<br>NEMA 12 |
| Material thickness - door | 2 mm |
| Material thickness - enclosure | 2 mm |
| Material thickness – mounting plate | 2.5 mm |
| Rated current | 0.68 A |
| Air throughput (unimpeded air flow) | 400 cfm |
| Fan size | 6 in |
| Packaging unit | 1 pc(s). |
| Customs tariff number | 9403999040 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |