

Rittal – The System.

Faster – better – everywhere.



IT 9982.124

Network/server enclosures TS IT

State: 2026-03-04 (Source: rittal.com/ca-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 9982.124 - Network/server enclosures TS IT with vented door, pre-configured, RAL 9005, North American version

TS IT pre-configured with standard accessories. RAL 9005 (Black). Enclosures are complete with depth variable 482.6mm (19") profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits.

Features

Model No.	IT 9982.124
Product description	TS IT pre-configured with standard accessories. RAL 9005 (Black). Enclosures are complete with depth variable 482.6mm (19") profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits.
Material	Carbon steel Aluminum
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 9005
Color	Enclosure frame and panels: RAL 9005 Interior installation: RAL 9005

Features

Supply includes	Enclosure frame TS 8 with door and roof plate Aluminum carbon steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges Carbon steel door at rear, ventilated in one piece (free area in perforated carbon steel part approx. 85 %), 130° hinges Front and rear comfort handles with push button keyed door lock Installed caster kits Installed leveling feet M6 cage nuts (Package of 100) M6 mounting screws (Package of 100) Solid sidewalls, pre-installed PDU brackets (shipped loose) Cable management wall, pre-installed
Dimensions	Width: 600 mm Height: 2,200 mm Depth: 1,050 mm
Installation height for components	47 U
Load capacity of the 19" levels	10,000 N
Note	The door-opening angle may vary depending on site requirements or applications with side panels
Distance between levels as delivered	745 mm
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Design doors	Vented
Packaging unit	1 pc(s).
Gross weight	362.95 lb
Customs tariff number	9403999040

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------