

Rittal – The System.

Faster – better – everywhere.



IT 9982.135

Network/server enclosures TS IT

State: 2025-07-06 (Source: [rittal.com/ca-en](https://www.rittal.com/ca-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 9982.135 - Network/server enclosures TS IT with vented door, pre-configured, RAL 7035, North American version

TS IT pre-configured with standard accessories. RAL 7035 (Light gray). Enclosures are complete with depth variable 482.6mm (19”) profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits.

Features

Model No.	IT 9982.135
Product description	TS IT pre-configured with standard accessories. RAL 7035 (Light gray). Enclosures are complete with depth variable 482.6mm (19”) profile rails, casters, cable management, PDU brackets and locking front and rear vented doors. Available in a range of size variants with optional sidewalls and baying kits.
Material	Carbon steel Aluminum
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors and roof: Dipcoat-primed, powder coated
General color	RAL 7035
Color	Interior installation: RAL 9005

Features

Supply includes	Enclosure frame TS 8 with door and roof plate Aluminum carbon steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges Carbon steel door at rear, ventilated in one piece (free area in perforated carbon steel part approx. 85 %), 130° hinges Front and rear comfort handles with push button keyed door lock Installed caster kits Installed leveling feet M6 cage nuts (Package of 100) M6 mounting screws (Package of 100) Solid sidewalls, pre-installed Dual cable management walls pre-installed with integrated PDU mounting points
Dimensions	Width: 800 mm Height: 2,200 mm Depth: 1,200 mm
Installation height for components	47 U
Height incl. base/plinth	2,300 mm
Load capacity of the 19" levels	10,000 N
Note	with side panels
Distance between levels as delivered	745 mm
Design of 19" mounting level(s)	Profile rails, 482.6 mm (19")
Design doors	Vented
Packaging unit	1 pc(s).
Gross weight	416.601
UPC-Code	90655

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------