

Rittal – The System.

Faster – better – everywhere.



JB 8018.152

Boîtes de raccordement JB

État: 2026-05-22 (La source: [rittal.com/ca-fr](https://www.rittal.com/ca-fr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



JB 8018.152 - Boîtes de raccordement JB 316 stainless steel

The JB enclosure offers protection for dense wiring and sensitive small instruments. These hinged cover junction boxes combine the advantages of the AE and KL series at an economical cost. Features include 180 degree hinge and slotted insert quarter turn latch. Foamed-in-place gasket and a knife-edge perimeter add extra protection.



Caractéristiques

Référence	JB 8018.152
Matériau	Acier inoxydable AISI 316L (1.4404)
Finition	Coffret et porte : brossé, grain 240
Composition de la livraison	Charnière 180° Plaque de montage
Épaisseur de matériau de la porte	1,5 mm
Épaisseur du coffret	1,5 mm
Position des charnières	à gauche
Dimensions	Largeur: 150 mm Hauteur: 200 mm Profondeur: 150 mm
Indice de protection IP selon la norme CEI 60 529	IP 66
Indice de protection NEMA	NEMA 4X
Unité d'emballage	1 p.
Poids net	4,85 lb

Caractéristiques

Poids brut	4,901 lb
Numéro du tarif douanier	8538100000

Approbation

Approbation	UL + C-UL (listed)
-------------	--------------------