

**Rittal – The System.**

Faster – better – everywhere.



**JB 8018.153**

**Boîtes de raccordement JB**

État: 2026-06-19 (La source: [rittal.com/ca-fr](https://www.rittal.com/ca-fr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# JB 8018.153 - Boîtes de raccordement JB 316 stainless steel

The JB enclosure offers protection for dense wiring and sensitive small instruments. These hinged cover junction boxes combine the advantages of the AE and KL series at an economical cost. Features include 180 degree hinge and slotted insert quarter turn latch. Foamed-in-place gasket and a knife-edge perimeter add extra protection.



## Caractéristiques

Référence	JB 8018.153
Matériau	Acier inoxydable AISI 316L (1.4404)
Finition	Coffret et porte : brossé, grain 240
Composition de la livraison	Charnière 180° Plaque de montage
Épaisseur de matériau de la porte	1,5 mm
Épaisseur du coffret	1,5 mm
Position des charnières	à gauche
Dimensions	Largeur: 250 mm Hauteur: 300 mm Profondeur: 200 mm
Indice de protection IP selon la norme CEI 60 529	IP 66
Indice de protection NEMA	NEMA 4X
Unité d'emballage	1 p.
Poids net	11,023 lb

# Caractéristiques

---

Poids brut	13,228 lb
Numéro du tarif douanier	8538100000

---

# Approbation

---

Approbation	UL + C-UL (listed)
-------------	--------------------