Rittal – The System.

Faster – better – everywhere.





SZ 2564.300 塑料电缆盖板

状态: 2025-12-17 (来源: rittal.com/cn-zh)



SZ 2564.300 - 塑料电缆盖板 配备隔膜,用于 AX

只能用一尖头插入塑料中,然后将电缆穿通拉过。

特征

0.7
1件
1 x 50-110
2 x 26-54
2 x 26-35
2 x 19-34
8 x 15-25
48 x 10-15
28 x 5-11
类型 12
类型 1
在按照规定安装时,防护等级为 IP 66
尺寸: 4
箱体类型: AX
深度: 149 mm
宽度: 534 mm
可在各箱体中获知各法兰板大小分类
与 RAL 7035 类似
塑料,根据 UL 94-V0
只能用一尖头插入塑料中,然后将电缆穿通拉过。
SZ 2564.300

© Rittal 2025 2

特征

毛重	0.736
税率号	39269097
EAN	4028177935723
E-Number Sweden	E3465291
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

批准

批准 UL + C-UL - FTTA