Rittal – The System.

Faster - better - everywhere.





IT 5302.042 19 英寸电缆桥架,可调深度

状态: 2025-11-26 (来源: rittal.com/cn-zh)



IT 5302.042 - 19 英寸电缆桥架,可调深度

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

特征

型号	IT 5302.042
您的获益	Cable entry at the front via brush strip for thermal partitioning of the cable entry zone Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear Fully depth-variable with versatile, infinitely adjustable extension of the cable link Prevents incorrect airflow by partitioning the transition Open at the top for easy retrofitting, even with cables already inserted Cable link extendible upwards by 1 U, by using an additional cable entry panel with brush strip
材料	钢板 刷条:塑料,符合 UL 94-V0
表面	喷漆
颜色	RAL 9005
供货范围	Cable link 刷条
安装可能性	用于固定前后 19" 的安装平面
层面间距	500 - 750 mm
高度单位	1 U

© Rittal 2025 2

特征

承载力(静态)	150 N
适用于	用于不受机柜影响的独立安装
说明	Assembly parts should be ordered separately
包装单元	1件
税率号	73269098

© Rittal 2025