

# Rittal – The System.

Faster – better – everywhere.



## IT 5302.042

## 19 英寸电缆桥架，可调深度

状态: 2026-2-11 (来源: [ittal.com/cn-zh](https://www.ittal.com/cn-zh))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# IT 5302.042 - 19 英寸电缆桥架，可调深度

Within the 482.6 mm (19") mounting level, the cable link provides an integrated cable routing option between the front and rear mounting levels inside an enclosure.

## 特征

|       |  |
|-------|--|
| 型号    | IT 5302.042  |
| 您的收益  | <p>Cable entry at the front via brush strip for thermal partitioning of the cable entry zone</p> <p>Direct cable routing between the patch level and component with rear installation, optimum cable routing with switch mounted at the rear</p> <p>Fully depth-variable with versatile, infinitely adjustable extension of the cable link</p> <p>Prevents incorrect airflow by partitioning the transition</p> <p>Open at the top for easy retrofitting, even with cables already inserted</p> <p>Cable link extendable upwards by 1 U, by using an additional cable entry panel with brush strip</p> |
| 材料    | <p>钢板</p> <p>刷条：塑料，符合 UL 94-V0</p>   |
| 表面    | 喷漆   |
| 颜色    | RAL 9005   |
| 供货范围  | <p>Cable link</p> <p>刷条</p>  |
| 安装可能性 | 用于固定前后 19" 的安装平面   |
| 层面间距  | 500 - 750 mm   |
| 高度单位  | 1 U  |

# 特征

|                     |   |
|---------------------|---|
| 承载力 (静态)            | 150 N                                       |
| 适用于                 | 用于不受机柜影响的独立安装                               |
| 说明                  | Assembly parts should be ordered separately |
| 包装单元                | 1 件   |
| 本型号 (含包装) PCF (出厂前) | PCF-Wert 18,78 kg Co <sup>2</sup> e         |
| 税率号                 | 73269098                                    |