Rittal – The System.

Faster – better – everywhere.





CX 6701.000 CX底座

状态: 2025-12-12 (来源: rittal.com/cn-zh)



CX 6701.000 - CX底座

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.







特征

	CX 6701.000
型式	下面部分
材料	箱体: 钢板 1.5 mm
	门:钢板,2.0 mm,周围用发泡聚氨酯塑料 (PU) 密封圈。
	安装板:钢板,2.5 mm
表面	箱体和门:浸涂底漆,外经粉末涂层 ,织纹
	安装板:镀锌
颜色	RAL 7035
供货范围	箱体上方敞开
	前单门/双门,配备三点式闭锁系统
	安装板
	底板
	锁: 3 mm 双齿

© Rittal 2025

特征

尺寸	宽度: 800 mm
	高度: 675 mm
	深度: 400 mm
安装板尺寸(宽 x 高)	720 mm x 625 mm
门数	1
开门角度	130°
IK 编码	IK10
说明	需要使用封板来封闭琴式控制台底部结构
	2段式琴式控制台结构需要一个琴式控制台中部结构和一个琴式控制
	台中部结构用的封板
	3 段式琴式控制台结构需要一个琴式控制台中部结构和琴式控制台上
	部结构
防护等级 IP,符合 IEC 60 529 标准	IP 55
Protection category NEMA	NEMA 1
	NEMA 12
基本材料	钢板
锁具数量	1
锁具规格	三点式锁具系统
锁芯	3 mm 双齿
 锁	锁具规格: 三点式锁具系统
	锁具数量: 1
	锁芯: 3 mm 双齿
包装单元	1件
净重	38.5
毛重	39.875
税率号	94032080

© Rittal 2025

特征

EAN	4028177983793
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

批准

批准	UL + C-UL (listed)
解释	符合性声明

© Rittal 2025 4