

# Rittal – The System.

Faster – better – everywhere.



## CX 6706.000

## CX底座

状态: 2026-4-3 (来源: [rittal.com/cn-zh](http://rittal.com/cn-zh))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CX 6706.000 - CX底座

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



## 特征

型号	CX 6706.000
型式	下面部分
材料	箱体：钢板 1.5 mm 门：钢板，2.0 mm，周围用发泡聚氨酯塑料 (PU) 密封圈。 安装板：钢板，2.5 mm
表面	箱体和门：浸涂底漆，外经粉末涂层，织纹 安装板：镀锌
颜色	RAL 7035
供货范围	箱体上方敞开 前单门/双门，配备三点式闭锁系统 安装板 底板 锁：3 mm 双齿

# 特征

尺寸	宽度: 1,200 mm 高度: 675 mm 深度: 500 mm
安装板尺寸 (宽 x 高)	1,120 mm x 625 mm
门数	2
开门角度	130°
IK 编码	IK10
说明	需要使用封板来封闭琴式控制台底部结构 2 段式琴式控制台结构需要一个琴式控制台中部结构和一个琴式控制台中部结构用的封板 3 段式琴式控制台结构需要一个琴式控制台中部结构和琴式控制台上部结构
防护等级 IP, 符合 IEC 60 529 标准	IP 55
Protection category NEMA	NEMA 1 NEMA 12
基本材料	钢板
锁具数量	1
锁具规格	三点式锁具系统
锁芯	3 mm 双齿
锁	锁具规格: 三点式锁具系统 锁具数量: 1 锁芯: 3 mm 双齿
包装单元	1 件
净重	60 kg
毛重	62.75 kg
税率号	94032080

## 特征

---

ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
产品描述	CX 琴式控制台系统, 琴式控制台底座, 宽 x 高 x 深: 1200 x 675 x 500 mm, 钢板

## 批准

---

批准	UL + C-UL (listed)
解释	符合性声明