

**Rittal – The System.**

Faster – better – everywhere.



# KL 1522.010

## Terminal boxes KL

State: 15/07/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1522.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | KL 1522.010   |
| Material                          | Enclosure: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish                    | Enclosure and cover: Brushed, grain 180   |
| Supply includes                   | Enclosure with cover<br>Quick-release fastener including plastic bushes   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |
| Dimensions                        | Width: 300 mm<br>Height: 150 mm<br>Depth: 80 mm   |
| Material thickness - cover        | 1.25 mm   |
| Material thickness - enclosure    | 1.25 mm   |
| Lock                              | Number of locks: 4  |
| Basic material                    | Stainless steel 1.4301 (AISI 304)   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 1.673   |
| Gross weight                      | 1.94  |
| Customs tariff number             | 84879090  |
| EAN                               | 4028177008465   |
| E-Number Sweden                   | E3404364  |
| ETIM 9                            | EC000261  |
| ETIM 8                            | EC000261  |

# Features

---

ECLASS 8.0

27180101

## Approvals

---

Approvals

Bureau Veritas  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

Explanations

Declaration of conformity  
Declaration of conformity UK

## Tender text

Stainless steel terminal box without gland plate,  
protection cat. IP 66

Enclosure:

of 1.25 mm stainless steel 1.4301 (AISI 304), folded  
and welded from a single piece, with all-round  
protection channel on the cover aperture. Cover of 1.25  
mm stainless steel, sealed, with foamed-in special  
cover seal, facilities for connecting PE conductors in  
the cover and box, profile strips on both internal  
sides with mounting holes. Special plastic bush guards  
against accidental loss of the cover screws and  
provides screwdriver guidance.

Accessories:

quick-release fastener, cover retainer, plastic cable  
gland plate, cover hinges, mounting plate

Surface finish:

brushed

Dimensions (W x H x D): 300 x 150 x 80 mm