

**Rittal – The System.**

Faster – better – everywhere.



**KL 1581.000**

**Plastic cable gland plates**

State: 06/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1581.000 - Plastic cable gland plates with PG knockouts

With pre-punched PG holes for cable glands.



## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | KL 1581.000   |
| Product description               | With pre-punched PG holes for cable glands. Use seal for standard gland plates. |
| Material                          | ABS   |
| Colour                            | RAL 7035  |
| Note                              | The allocation of gland plate sizes is indicated on the relevant enclosures     |
| No. of metric knockouts           | 12  |
| Number x PG diameter              | 12 x 13.5   |
| Dimensions                        | Width: 220 mm<br>Depth: 90 mm   |
| To fit                            | Enclosure type: KL  |
| Gland plate                       | Size: 2   |
| Operating temperature range       | -40 °C...70 °C  |
| Protection category to IEC 60 529 | IP 55 if installed correctly  |
| Packs of                          | 5 pc(s).  |
| Net weight                        | 0.505 kg  |

# Features

---

|                       |  |
|-----------------------|--|
| Gross weight          | 0.604 kg   |
| Customs tariff number | 73079100   |
| ETIM 9                | EC000211   |
| ETIM 8                | EC000211   |
| ECLASS 8.0            | 27142421   |
| Product description   | KL Plastic cable gland plate, with PG knock-outs, WD: 220x90 mm, size: 2, PG knockouts: 13.5 |