Rittal – The System.

Faster – better – everywhere.





SZ 1581.200 Metal gland plate

State: 04/12/2025 (Source: rittal.com/com-en)



SZ 1581.200 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

SZ 1581.200
Simply knock out the holes for the cable glands using a screwdriver.
Sheet steel
RAL 7035
The allocation of gland plate sizes is indicated on the relevant enclosures
12 x M20
Width: 220 mm Depth: 90 mm
Enclosure type: KX
IP 55 if installed correctly
Type 1 Type 12K
12
M20
1 pc(s).
0.23
0.24
1.2 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
73079100
4028177940536

© Rittal 2025

Features

E-Number Sweden	E3465317
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3