Rittal – The System.

Faster – better – everywhere.

BG 1605.520

Bus enclosures BG

State: 03/11/2026 (Source: www.rittal.com/com-en)

BG 1605.520 - Bus enclosures BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

Model No.	BG 1605.520
Material	Enclosure: Sheet steel Door: Sheet steel Viewing window: Polycarbonate, 4 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint
Colour	RAL 7035
Supply includes	Enclosure with door Viewing window in the door
Dimensions	Width: 200 mm Height: 300 mm Depth: 120 mm
Protection category to IEC 60 529	IP 65
Protection category NEMA	NEMA 12
IK Code	IK08
Material thickness - enclosure	1.25 mm
Material thickness - door	1.25 mm
Door hinge position	right
Number of support rails	1
Cut-outs (quantity x diameter)	2
Lock	Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit
Cable entry (quantity x diameter)	2 x M12 M32

© Rittal 2026

Features

Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	2.546 kg
Gross weight	2.667 kg
Customs tariff number	94032080
ECLASS 8.0	27180101
Product description	BG Bus enclosure, WHD: 200x300x120 mm, Sheet steel, with metric holes in the base and support rail, Door with viewing window, hinged on the right

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity