

# Rittal – The System.

Faster – better – everywhere.



## EL 2092.500 Captive nuts

State: 05/07/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# EL 2092.500 - Captive nuts

Captive nut, with M5 thread, without contact

## Features

|                          |  |
|--------------------------|--|
| Model No.                | EL 2092.500  |
| Design                   | without contact  |
| Product description      | For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure. |
| Dimensions               | Thread: M5   |
| For material thicknesses | 0.8 - 2.5 mm   |
| Packs of                 | 50 pc(s).  |
| Net weight               | 0.15 kg  |
| Gross weight             | 0.221 kg   |
| Customs tariff number    | 73181692   |
| ETIM 9                   | EC002358   |
| ETIM 8                   | EC002358   |
| ECLASS 8.0               | 23110815   |
| Product description      | EL Captive nuts, M5, Without contact, For metal thickness: 0,8-2 mm  |