

# Rittal – The System.

Faster – better – everywhere.



## EL 2094.500 Captive nuts

State: 13/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# EL 2094.500 - Captive nuts

Captive nut, with M5 thread, with contact

## Features

Model No.	EL 2094.500
Design	with contact
Product description	For the attachment of rack-mounted electronic equipment, 482.6 mm (19") installed equipment and blanking plates to mounting angles, 482.6 mm (19"). For use with metal thickness from 0.8 – 2.5 mm. Optionally with or without contact of the installed equipment to the 482.6 mm (19") section/enclosure.
Dimensions	Thread: M5
For material thicknesses	0.8 - 2.5 mm
Packs of	50 pc(s).
Net weight	0.2 kg
Gross weight	0.25 kg
Customs tariff number	73181692
ETIM 9	EC002358
ETIM 8	EC002358
ECLASS 8.0	23110815
Product description	EL Captive nuts, M5, With contact, For metal thickness: 0,8-2 mm