


**Rittal – The System.**

Faster – better – everywhere.



**EL 2256.605**

**Wall-mounted enclosures EL, 3-part**

State: 18/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# EL 2256.605 - Wall-mounted enclosures EL, 3-part with mounting plate and mounting angles, static installation

Wall-mounted enclosure 3-part, pre-configured with: Solid gland plate, top and bottom, mounting plate is supplied loose. Protection category IP 55.

## Features

Model No.	EL 2256.605
Design	Wall-mounted enclosures IT with mounting plate and mounting angles, static installation
Product description	Wall-mounted enclosure with optimum accessibility due to hinged part.
Material	Wall and hinged part: Sheet steel, 1.5 mm Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
General colour	RAL 7035
Colour	Wall and hinged part: RAL 7035 Glazed door: RAL 7035/7015 (slate grey)
Supply includes	Wall section with solid gland plate, top and bottom and mounting plate (supplied loose). Hinged part with 25 mm pitch pattern of holes in the front and rear frame, and two 482.6 mm (19") mounting angles, front, static installation Designer glazed door 1 double-kit key no. 5 Mini-comfort handle for lock inserts Security lock 3524 E
Units	6 U
Dimensions	Width: 600 mm Height: 345 mm Depth: 473 mm
Installation depth	420 mm

# Features

---

Clearances	Clearance width: 502 mm Clearance height: 282 mm
Depth hinged part	316 mm
Dimensions mounting plate (W x H)	485 mm x 299 mm
Depth of wall section	135 mm
IK Code	IK08
Load capacity of hinged part (static)	300 N
Basic material	Sheet steel
Protection category to IEC 60 529	IP 55
Packs of	1 pc(s).
Net weight	25.969 kg
Gross weight	27.336 kg
Customs tariff number	94032080
ETIM 9	EC002500
ETIM 8	EC002500
ECLASS 8.0	27180208
Product description	EL Wall-mounted enclosures, 3-part, 6 U, WHD: 600x345x473 mm, Protection category: IP 55, Designer glazed door

# Approvals

---

Approvals	Lloyds Register of Shipping UL + C-UL (listed)
-----------	---

# Tender text

Wall-mounted enclosure Electronic Kombi System,  
preconfigured, 6 U

Enclosure: 3-part wall-mounted enclosure consisting of:

Wall section with solid gland plate at the top and  
bottom, may optionally be exchanged for cable entry  
variants (accessories), holes for wall-mounting,  
1 mounting plate (supplied loose)

Hinged section with 2 mounting angles,  
482.6 mm (19 inch), fitted,  
with all-round 25 mm pitch pattern of holes  
in the front and rear frame,

designer glazed door with mini comfort handle  
for lock inserts, with security lock 3524 E,  
may optionally be exchanged for mini comfort handle for  
semi cylinder

Protection category: IP 55 to EN 60 529/10.91

Load capacity of hinged part: 30 kg

Material

Enclosure: 1.5 mm sheet steel

Mounting plate: 2.5 mm sheet steel

Viewing window: 3 mm safety glass

Surface finish

Electrophoretic dipcoat-primed, spray-finished,  
enclosure in RAL 7035, glazed door in RAL 7035/7015,  
zinc-plated mounting plate

Dimensions (W x H x D): 600 x 345 x 473 mm (6 U)