


# Rittal – The System.

Faster – better – everywhere.



## SG 2370.151

### LED steady light component

State: 08/09/2025 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2370.151 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | SG 2370.151   |
| Design                            | LED steady light component  |
| Benefits                          | With 360° signal transmission thanks to optimised prism system<br>Configuration of up to five components with the same voltage. |
| Function principle                | A modular layout is possible with connection, optical and acoustic components and a label panel                                 |
| Material                          | Enclosure of polyamide<br>Cap: Transparent polycarbonate  |
| Colour                            | Red   |
| Protection category to IEC 60 529 | IP 65 if a cover or acoustic component is fitted at the top   |
| Rated operating voltage           | 230 V   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0.069   |
| Gross weight                      | 0.075   |
| Customs tariff number             | 85311095  |
| EAN                               | 4028177953598   |
| ETIM 9                            | EC000232  |
| ETIM 8                            | EC000232  |
| ECLASS 8.0                        | 27371220  |

## Approvals

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |