Rittal – The System.

Faster – better – everywhere.



SG 2376.001

Acoustic component

State: 18/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SG 2376.001 - Acoustic component for signal pillar, modular

To indicate warnings or malfunctions.

Features

Model No.	SG 2376.001
Design	Continuous tone or pulsating, 105 dB
Product description	To indicate warnings or malfunctions.
Material	Enclosure of polyamide
Colour	Black
Assembly instruction	Mounting only on the upper end of the optical components or directly on the connection component.
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V
Packs of	1 pc(s).
Net weight	0.079 kg
Gross weight	0.089 kg
Customs tariff number	85311095
ETIM 9	EC001261
ETIM 8	EC001261
ECLASS 8.0	27371237
Product description	SG acoustic component, 95 - 105 dB

Approvals

Approvals	UL + C-UL (listed)

Approvals

Explanations

Declaration of conformity

© Rittal 2026