
Rittal – The System.

Faster - better - everywhere.





AX 2473.010 Protective roof


State: 29/10/2025 (Source: rittal.com/com-en)



AX 2473.010 - Protective roof for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.







Features

AX 2473.010
The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.
Stainless steel 1.4301 (AISI 304)
Brushed, grain 240
Assembly parts
May also be screw-fastened for dynamic loads
Height: 37 mm
Type 1
Type 3R
Type 4
Type 4X
Type 12
Enclosure type: AX
Width: = 600 mm
Depth: = 210 mm
1 pc(s).
2.12

© Rittal 2025

Features

Gross weight	2.34
Customs tariff number	94039910
EAN	4028177938236
E-Number Sweden	E3465265
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

Approvals

Approvals UL + C-UL - FTTA