Rittal – The System.

Faster – better – everywhere.





SZ 2474.000 Protective roof

State: 05/12/2025 (Source: rittal.com/com-en)



SZ 2474.000 - Protective roof for AE

Reliable protection for outdoor siting – with water run-off to the rear. Material: Stainless steel 1.4301 (AISI 304)

Features

Model No.	SZ 2474.000
Product description	Reliable protection for outdoor siting – with water run-off to the rear. Easily retro-fitted.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 240
Supply includes	Assembly parts
Note	For outdoor siting, we generally recommend a rain canopy above the enclosure or the gap between the door and the enclosure, in order to protect against water and UV radiation. Testing of IP protection categories for water protection (2nd code number to IEC 60 529) cannot be compared with an enclosure sited outdoors or under similar conditions Depending on the ambient conditions, additional measures may be required
To fit	Enclosure type: AE stainless steel Width: = 760 mm Depth: = 300 mm
Packs of	1 pc(s).
Net weight	3.21
Gross weight	3.5
Customs tariff number	94039910
EAN	4028177024540
E-Number Sweden	E3404546
ETIM 9	EC000744
ETIM 8	EC000744

© Rittal 2025

Features

ECLASS 8.0

27182405

© Rittal 2025 3