

# Rittal – The System.

Faster – better – everywhere.



## SZ 2563.300 Plastic gland plate

State: 06/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2563.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

## Features

Model No.	SZ 2563.300
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.
Material	Plastic to UL 94-V0
Colour	Similar to RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 447 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 3
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12
No. of cable entries and Ø (mm) min.-max.	36 x 5-11 46 x 10-15 8 x 15-25 2 x 19-34 4 x 26-35 2 x 26-54
Packs of	1 pc(s).
Net weight	0.61 kg
Gross weight	0.63 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211

# Features

---

ECLASS 8.0

27142421

---

Product description

SZ Plastic gland plates, for AX, with membranes, WD: 447x149 mm,  
for gland plates size 3

# Approvals

---

Approvals

UL + C-UL - FTTA