

Rittal – The System.

Faster – better – everywhere.



AX 2584.100 Pole clamp

State: 17/04/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2584.100 - Pole clamp for AX, KX, AX plastic, AX IT, CS wall-mounted enclosures

For reliable, convenient fastening to round or square poles.



Features

| | |
|--------------------------|---|
| Model No. | AX 2584.100 |
| Product description | For reliable, convenient fastening to round or square poles. |
| Technical specifications | For pole diameter: Ø from 40 to 170 mm For pole size: □ from 50 to 150 mm |
| Material | Mounting angles, clamping section: Sheet steel Clamping strap: Stainless steel 1.4301 (AISI 304) |
| Surface finish | Mounting angle, clamp strip: Galvanic zinc-nickel, passivated |
| Supply includes | 2 mounting angles, 600 mm long 4 clamping sections 2 clamping straps 4 clamping brackets 4 self-tapping M10 bolts for mounting onto the enclosure |
| Note | Only suitable for enclosures up to a width of 600 mm. |

Features

| | |
|-------------------------------|--|
| To fit | Enclosure type: AX KX AX plastic AX IT CS wall-mounted enclosures AX outdoor housing AE KL EB AX wall-mounted enclosure, 3-part |
| Type rating to UL 50E | Type 1 Type 3R Type 4 Type 12 |
| Packs of | 2 pc(s). |
| Net weight | 1.88 kg |
| Gross weight | 1.96 kg |
| PCF per pack (cradle-to-gate) | 7.3 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 83024900 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189234 |
| Product description | AX Pole clamp |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|