


Rittal – The System.

Faster – better – everywhere.



FT 2787.000 Acrylic glazed cover

State: 02/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2787.000 - Acrylic glazed cover

For the protection of display and control components in standard 482.6 mm (19") or metric sizes.

Features

Model No.	FT 2787.000
Design	Metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminium sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly parts. Lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
Dimensions	Width: 500 mm Height: 400 mm Depth: 47.5 mm
Visible area	Viewing window width: 460 mm Viewing window height: 379.5 mm
Build depth for components (max.)	43 mm
Packs of	1 pc(s).
Net weight	2.228 kg
Gross weight	2.428 kg
Customs tariff number	39205100
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301
Product description	FT Acrylic glazed cover, 482.6 mm (19"), WHD: 500x400x47,5 mm