

Rittal – The System.

Faster – better – everywhere.



FT 2793.560 Viewing window

Source: 13/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2793.560 - Viewing window Stainless steel

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access. Made from stainless steel 1.4301 (AISI 304).



Features

| | |
|-----------------------------------|---|
| Model No. | FT 2793.560 |
| Product description | Fitted as standard with internal 130° hinges and all-round seal. |
| Material | Stainless steel 1.4301 (AISI 304) Single-pane safety glass |
| Supply includes | Assembly parts |
| Protection category to IEC 60 529 | IP 54 |
| Note | Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm). |
| Dimensions | Width: 522 mm Height: 600 mm Depth: 38 mm |
| Visible area | Viewing window width: 408 mm Viewing window height: 543 mm |
| Build depth for components (max.) | 31 mm |

Features

| | |
|-----------------------|---|
| Packs of | 1 pc(s). |
| Net weight | 6.175 kg |
| Gross weight | 6.5 kg |
| Customs tariff number | 76101000 |
| ETIM 9 | EC002527 |
| ETIM 8 | EC002527 |
| ECLASS 8.0 | 27182204 |
| Product description | FT Viewing window, WHD: 522x600x38 mm, Stainless steel 1.4301 |