

# Rittal – The System.

Faster – better – everywhere.



## SV 3073.000 Busbar support

State: 18/04/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 3073.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



## Features

Model No.	SV 3073.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole 100 mm
To fit busbars	30 x 10 40 x 10 50 x 10 60 x 10
Rated current max.	1,250 A
Dimensions	Width: 22 mm Height: 320 mm Depth: 70 mm
Packs of	4 pc(s).
Net weight	1.612 kg
Gross weight	1.83 kg
Customs tariff number	85469010
ETIM 9	EC001166
ETIM 8	EC001166

# Features

---

ECLASS 8.0

27400607

---

Product description

SV Busbar support, 3-pole, 100 mm bar centre distance, for busbar  
WH: 30-60x10 mm

# Approvals

---

Explanations

Declaration of conformity

Declaration of conformity UK

# Tender text

SV busbar support

for accommodating busbars. 3-pole busbar support  
with 100 mm bar centre distance.

Rated operating voltage: 1000 V~, 50/60 Hz  
to VDE 0660

Rated current: up to 1250 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 100 mm

Bar accommodation without inserts: 60 x 10 mm

Tightening torques

Assembly screws: 8 - 10 Nm

Lid attachment: 1 - 3 Nm

Approvals:

DNV, GL, VDE, ÖVE, SEV, KEMA