

# Rittal – The System.

Faster – better – everywhere.



## SK 3201.050 Chopped-fibre filter mat

State: 17/08/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3201.050 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.



## Features

Model No.	SK 3201.050
Design	for Thermoelectric Cooler
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3201.200 3201.300
Dimensions	Width: 90 mm Height: 106 mm Depth: 8 mm
Filter class	to DIN EN 779: G2
Packs of	5 pc(s).
Net weight	0.01
Gross weight	0.014

# Features

Customs tariff number	56039390
EAN	4028177598676
E-Number Sweden	E3404569
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

# Approvals

Certificates	EAC
--------------	-----