


**Rittal – The System.**

Faster – better – everywhere.



**SK 3237.054**

**Chopped-fibre filter mat**

State: 28/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3237.054 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Model No.	SK 3237.054
Design	for filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Chemical fibres
Colour	White
Note	No suitable for use in EMC filter fans.
To fit Model No.	3237.3xx/3237.7xx
Dimensions	Width: 89 mm Height: 89 mm Depth: 10 mm
Filter class	to DIN EN 779: G2 to DIN EN ISO 16890: ISO Coarse 50%
Packs of	5 pc(s).
Net weight	0.005 kg
Gross weight	0.012 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

# Features

---

Product description	SK Chopped-fibre filter mat, for fan-and-filter units SK 3237.7xx/3237.3xx, WxHxD: 89 x 89 x 10 mm
---------------------	----------------------------------------------------------------------------------------------------

# Approvals

---

Approvals	UR + C-UR (recognized)
-----------	------------------------