
## Rittal - The System.

Faster – better – everywhere.





# SK 3243.308 Blue e+ outlet filter

State: 21/11/2025 (Source: rittal.com/com-en)




#### SK 3243.308 - Blue e+ outlet filter

The outlet filter is used in conjunction with the corresponding fan-and-filter unit to dissipate heat loss from enclosures, ventilate the enclosure and protect temperature-sensitive components. This is achieved through the direct infeed of ambient air, the temperature of which must be lower than the permissible internal temperature of the enclosure.







#### **Features**

Model No.	SK 3243.308
Design	wall-mounted
Benefits	Easy filter changes, thanks to a new opening mechanism on the
	louvred grille
	Faster installation on the enclosure with optimised detent hooks
	Tool-free assembly
Material	Plastic
Colour	RAL 9005
Supply includes	Outlet filter
	Pleated filter
Mounting cut-out	Cut-out width: 292 mm
	Cut-out height: 292 mm
To fit Model No.	SK 3243.7xx/3243.9xx/3244.7xx/3244.9xx/3245.9xx
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 44.7 mm

© Rittal 2025 2

### Features

Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose- proof hood
IP protection category to IEC 60	IP 54 with chopped-fibre filter/pleated filter
529	IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Packs of	1 pc(s).
Net weight	0.94
Gross weight	0.95
Customs tariff number	39269097
EAN	4028177998322
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

## Approvals

Approvals	UL + C-UL - FTTA
	UR + C-UR (recognized)

© Rittal 2025 3