

Rittal – The System.

Faster – better – everywhere.



SK 3301.390 Vertical shielding

State: 01/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3301.390 - Vertical shielding for TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

Features

Model No.	SK 3301.390
Design	Self-adhesive on one side
Product description	To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.
Material	Cellular PU foam Flame-inhibiting to UL 94 (HF1)
Colour	Anthracite
Sealing between	Side panel and 482.6 mm (19") level
Dimensions	Width: 184 mm Height: 1,910 mm Depth: 84 mm
To fit	Width: 800 mm
Packs of	1 pc(s).
Net weight	0.818 kg
Gross weight	0.918 kg
Customs tariff number	39269097
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	SK Vertical shielding, Sealing between side panel/LCP and 482.6 mm (19") level, WHD: 184x1910x84 mm, Cellular PU foam, self-adhesive on one side

Tender text

Thin foam rubber, 800 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 82.6 mm (19 inch) level. For 800 mm wide enclosures.

Length: 1900 mm, self-adhesive

Packs of 1