Rittal – The System.

Faster – better – everywhere.



# SK 3301.505

# Electric condensate evaporator

State: 07/11/2026 (Source: www.rittal.com/com-en)

# SK 3301.505 - Electric condensate evaporator

For external mounting on the enclosure. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted).



## Features

| | |
|---|---|
| Model No. | SK 3301.505 |
| Product description | For external mounting on the enclosure. For use with all enclosure cooling units and air/water heat exchangers (wall-mounted). |
| Benefits | Suitable for international use thanks to multi-voltage support |
| Colour | RAL 7035 |
| Supply includes | Electric condensate evaporator, ready to connect. |
| Evaporation performance | 230 V: 3,5 l/d<br>115 V: 3.0 l/d |
| Dimensions | Width: 400 mm<br>Height: 129 mm<br>Depth: 105 mm |
| Operating temperature range | 5 °C...60 °C |
| Rated operating voltage | 115 V - 230 V, 1~, 50 Hz/60 Hz |
| Packs of | 1 pc(s). |
| Net weight | 1.74 kg |
| Gross weight | 2.2 kg |
| Customs tariff number | 84189910 |
| ETIM 9 | EC002009 |

# Features

| | |
|---|---|
| ETIM 8 | EC002009 |
| ECLASS 8.0 | 27180715 |
| Product description | SK Electric condensate evaporator, 115-230 V, 1~, 50/60 Hz, WHD: 400 x 129 x 105 mm |

# Approvals

| | |
|---|---|
| Explanations | Declaration of conformity |

© Rittal 2026