


# Rittal – The System.

Faster – better – everywhere.



## HD 4000.075

# Fire extinguisher enclosure HD

State: 14/05/2026 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.075 - Fire extinguisher enclosure HD

Important security equipment is rapidly accessible and hygienically protected. The fire extinguisher housing may be sited directly in the production environment.

## Features

Model No.	HD 4000.075
Product description	Roof angled forwards by 30°
Benefits	Hygienic, hose-proof storage of fire extinguishers Time and cost savings thanks to simple, effective cleaning options Fire extinguisher is easily removed with one hand thanks to the T handle Quick inventory check with the integral viewing door
Material	Enclosure and door: Stainless steel 1.4301 (AISI 304) Handle and lock: Stainless steel 1.4301 (AISI 304) Viewing window: Polycarbonate Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Seal: Blue, dyed (RAL 5010)
Supply includes	Enclosure of all-round solid construction Door with viewing window and inserted seal Interchangeable door hinge T handle with 3-point lock system
Dimensions	Width: 390 mm Height, front: 840 mm Height rear: 1,010 mm Depth: 300 mm
Visible area	Viewing window width: 170 mm Viewing window height: 670 mm
Packs of	1 pc(s).
Net weight	20 kg
Gross weight	22 kg

# Features

---

Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------