

Rittal – The System.

Faster – better – everywhere.



HD 4000.240

Levelling feet HD

State: 10/02/2026 (Source: rittal.com/com-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

HD 4000.240 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

Model No.	HD 4000.240
Design	without base mount
Benefits	<p>Minimises cleaning time thanks to fully covered, permanently sealed threads</p> <p>Compensation of floor inclines up to an angle of 10° thanks to flexible base</p> <p>Baying can even be achieved on sloping floors, thanks to a large levelling range</p> <p>Certification to 3-A Sanitary Standards</p>
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly parts and seals
Load capacity	Max. 7000 N static per levelling foot
Dimensions	Thread: M12
To fit	Enclosure type: HD compact enclosure VX VX SE TS
Levelling range	122 - 175 mm
Packs of	4 pc(s).
Net weight	2
Gross weight	2.342
Customs tariff number	73181900
EAN	4028177707641
ETIM 9	EC002622
ETIM 8	EC002622

Features

ECLASS 8.0

27189263