

Rittal – The System.

Faster – better – everywhere.



AS 4055.163

Splitter hole punch, round

State: 10/07/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.163 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.163
Design	With triple splitting
Product description	
Supply includes	Female dies Male dies
Machinable material	Stainless steel
Maximum machinable material thickness, stainless steel	2.5 mm
Ø punch	63.5 mm
For threads	M63
Note	When operating with wrenches, tension screws with ball bearings should be used.
Suitable for hydraulic bolt order number	4055.663
Tension screw (Ø x L)	19 x 75 mm
Hydraulic tension screw Ø	19 mm
Packs of	1 pc(s).
Net weight	1.025 kg
Gross weight	1.098 kg
Customs tariff number	82073010
ETIM 9	EC000156
ETIM 8	EC000156

Features

ECLASS 8.0

21049047

Product description

Splitter hole punch, round for stainless steel, round, with triple splitting