Rittal – The System.

Faster - better - everywhere.





SZ 4139.350 Courtesy light

State: 26/11/2025 (Source: rittal.com/com-en)



SZ 4139.350 - Courtesy light

Supply voltage: 100 - 240 V AC 50/60 Hz

Features

Model No.	SZ 4139.350
Design	with door-operated switch
Supply includes	Courtesy light
	Light
	Light cover
	Assembly parts
	Integral door-operated switch
Power consumption	30 W
Ballast	Wide-range electronic ballast
Connection options	Power supply via connectors
	Through-wiring (creating rows of lights)
Integral door-operated switch	Yes
Light	Fluorescent lamp, base G13
Protection class	I (PE conductor)
Switch (type)	Integral on/off/door-operated switch
Light cover	Yes
Light – installation type	Screw-fastening
Rated impulse withstand voltage, phase to earth	2000 V AC
Rated impulse withstand voltage, phase to phase	1000 V AC
Rated insulation voltage	500 V DC/1s

© Rittal 2025

Features

Installation options	TS horizontal section of the roof frame: direct
	TS, SE vertical section: with TS adaptor bracket
	SE sections at the front and rear of the roof frame: with TS adaptor
	bracket
	SE extrusions at the side of the roof frame: direct
Dimensions	Width: 987 mm
	Height: 117 mm
	Depth: 50 mm
Operating temperature range	-15 °C45 °C
Sockets	D, earthing-pin (type F, CEE 7/4)
Storage temperature range	-20 °C70 °C
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz
Socket version	D, earthing-pin (type F, CEE 7/4)
Packs of	1 pc(s).
Net weight	2
Gross weight	2.26
Customs tariff number	94054990
EAN	4028177320765
ECLASS 8.0	27189241

Approvals

Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3