


# Rittal – The System.

Faster – better – everywhere.



## DK 5501.430

### Slide rail, 1 U, static installation

State: 13/07/2025 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 5501.430 - Slide rail, 1 U, static installation for VX IT, TS IT, TX CableNet

For mounting between a front and a rear pair of mounting angles.

## Features

|                                  |   |
|----------------------------------|---|
| Model No.                        | DK 5501.430   |
| Product description              | Side system punchings for mounting accessories and cooling components that expel to the side.   |
| Benefits                         | Simply locate into the system punchings of the 482.6 mm (19") mounting brackets after adjusting the required 482.6 mm (19") distance between levels |
| Applications                     | For mounting on the front mounting level<br>To support heavy installed equipment  |
| Material                         | Sheet steel   |
| Surface finish                   | Zinc-plated   |
| Supply includes                  | Assembly parts  |
| Distance between mounting levels | 545 mm  |
| Length                           | 475 mm  |
| Installation options             | for 482.6 mm (19") mounting angles, standard  |
| Assembly instruction             | The 482.6 mm (19") spacing between levels in the VX IT must be adjusted accordingly prior to installation   |
| Load capacity                    | 800 N, static   |
| Note                             | Effective contact surface 35 mm per side  |
| Contact surface                  | Width: 35 mm  |
| To fit                           | Enclosure type: VX IT<br>TS IT  |
| Packs of                         | 2 pc(s).  |
| Net weight                       | 1.2   |

# Features

|                               |  |
|-------------------------------|--|
| Gross weight                  | 1.4  |
| PCF per pack (cradle-to-gate) | 4.9 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 73269098   |
| EAN                           | 4028177678989  |
| E-Number Sweden               | E7239601   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |