Rittal - The System.

Faster – better – everywhere.





TP 6701.600 Pedestals

State: 23/10/2025 (Source: rittal.com/com-en)



TP 6701.600 - Pedestals

TopConsole pedestals, four widths and two different depths provide the basis for every TopConsole solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.

Features

Model No.	TP 6701.600
Material	Enclosure: Sheet steel 1.5 mm
	Door and console cover: Sheet steel, 2.0 mm, all-round foamed-in PU seal
	Mounting plate: Sheet steel
Surface finish	Enclosure, cover and door: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure open at top
	Door or double door with locking rod (with depth 400 mm at the
	front, with depth 500 mm at the front and rear)
	Mounting plate
	Gland plates
Dimensions mounting plate (W x H)	699 mm x 625 mm
Number of doors	1
Dimensions	Width: 800 mm
	Height: 675 mm
	Depth: 400 mm
IP protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Note	Positioning slide VX 5051.172 can be used as a mounting aid for base/plinth system VX in its new design
 Packs of	<u> </u>
	1 pc(s).

© Rittal 2025

Features

Net weight	40.66
Gross weight	41.66
Customs tariff number	94032080
EAN	4028177959859
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3