Rittal – The System.

Faster – better – everywhere.



DK 7030.080

CMC III programming cable

State: 05/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7030.080 - CMC III programming cable

For first-time commissioning of the Processing Unit (PU) or PU Compact.

Features

Model No.	DK 7030.080
Product description	For first-time commissioning of the Processing Unit (PU) or PU Compact. During initial start-up, the programming cable connects the CMC III Processing Unit/Compact to the USB interface of a PC. A driver for Windows systems is also included with the supply and must be installed on the PC.
Supply includes	CD-ROM with USB driver software System description
Length	3 m
Dimensions	Length: 3 m
Interfaces/connections	Connector (type): USB-AMini USB
Operating temperature range	0 °C...55 °C
Ambient humidity (non-condensing)	5...95 %
Packs of	1 pc(s).
Net weight	0.099 kg
Gross weight	0.113 kg
CRA risk class	Default (Low Risk)
Customs tariff number	85444290
ETIM 9	EC000313
ECLASS 8.0	27189253
Product description	DK CMC III programming cable USB, For commissioning the CMC III Processing Units, L: 3 m, 1 x USB series A, 1 x Mini USB

Tender text

7030.080
CMC III programming cable
Packs of 1
The programming cable is required for commissioning of the Processing Unit (PU) or PU Compact. A CD with USB driver software is also enclosed with the cable.
Technical specifications:
Connector 1: USB series A (for laptop)
Connector 2: Mini USB (for CMC III PU)
Length: 3 m
Temperature application range:
0 °C to 55 °C
Humidity range:
5% to 95% relative humidity, non-condensing
Included in the pack: Cable, quick reference guide and CD