

Rittal – The System.

Faster – better – everywhere.



DK 7030.240 Door kit

State: 20/06/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7030.240 - Door kit for TS IT

Gas pressure damper system, allowing the door to be opened in any emergency situation. The door kit is connected and activated using the corresponding door control module.

Features

Model No.	DK 7030.240
Design	for 1-piece aluminium glazed door
Product description	For automatic opening of a rack's doors in emergency situations. Connected and activated via the Door Control Module.
Function principle	The doors are kept closed by a magnetic system. If the power supply to the magnets is interrupted, the gas pressure damper system pushes the door open.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	with gas pressure damper system Cable harness Magnetic lock Assembly parts
Packs of	1 pc(s).
Weight/pack	3.34 kg
Customs tariff number	83015000
EAN	4028177695856
ETIM 7.0	EC001770
ECLASS 8.0	27390190

Approvals

Explanations	Declaration of conformity
--------------	---------------------------

Tender text

7030.240

Door kit for TS IT

Packs of 1 kit

To automatically open the doors in TS IT racks. Suitable for the TS IT rack with one-piece glazed door. The kit contains a gas pressure damper which constantly pushes the door open. The electric solenoids keep the door shut until the power supply is interrupted. The kit consists of a gas pressure damper, cable harness, 3 electro-magnetic locks and assembly parts.

Technical specifications:

Temperature application range:

-5 °C to 45 °C

Humidity range:

5% to 95% relative humidity, non-condensing

Rated voltage: 24 V DC

Rated current: 390 mA