
Rittal – The System.

Faster – better – everywhere.



# DK 7119.400

# Component shelf 2 U, static installation


State: 07/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7119.400 - Component shelf 2 U, static installation

Component shelf 2 U, static installation for attachment to the 482.6 mm (19") system punchings. Load capacity: 25 kg.





## Features

| | |
|---|---|
| Model No. | DK 7119.400 |
| Design | 482.6 mm (19") |
| Product description | For mounting between 482.6 mm (19") mounting angles. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm<br>Depth: 400 mm |
| Units | 2 U |
| Packs of | 1 pc(s). |
| Net weight | 3.19 kg |
| Gross weight | 3.58 kg |
| PCF per pack (cradle-to-gate) | 12.9 kg CO2 eq (Cat B) |

# Features

| | |
|---|---|
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | DK Component shelf, WHD: 482,6x2 Ux400 mm, 25 kg, static, distance between levels:, static installation, For 482.6 mm (19") system punchings, RAL 7035 |

# Tender text

Component shelf, 2 U, static, 400 mm deep

Load capacity: 25 kg surface load, static
Material: Sheet steel, spray finished in RAL 7035
Dimensions (W x H x D): 483 mm x 88 mm x 400 mm